



Gerber Plastigraphix™ LexEdge™ Clear

Description	1
Intended Applications	1
Printing	1
Cutting	2
Shelf Life and Storage	2
Maintenance	2
Chemical Resistance (Unprinted)	3
Related Literature (Product Bulletins)	3

DESCRIPTION

LexEdge Clear is a custom-formulated, 10 mil clear Lexan® based polycarbonate (GE Lexan 8010) designed for use with Gerber Digital Color Printing Systems and GerberColor™ foils. LexEdge Clear is dimensionally stable and resists tearing, abrasion, and heat. LexEdge Clear also has a protective, removable mask on the print side of the material.

INTENDED APPLICATIONS

LexEdge Clear is ideally suited for the production of architectural signage, point-of purchase displays, exhibit graphics, and membrane switch applications.

Continuous exposure to ultra-violet light may cause discoloration. LexEdge Clear is therefore not recommended for outdoor or backlit applications.

PRINTING

A tension roll holder should be used with LexEdge Clear.

LexEdge Clear is rolled print side out. Because both sides of the material are polished, the protective mask indicates the print side of the material. Before printing, remove the protective mask from the surface of the intended print area of the film. The mask is easy-to-remove and should only be taken off immediately before printing. The mask should remain on any unused material to ensure maximum protection during storage.

Fine particles may be attracted to the surface of this material. If this occurs, LexEdge Clear can be cleaned with distilled water and a lint-free cloth. Allow the material to completely dry before printing. Do not use an alcohol or solvent based cleaner on this product as they will cause the surface to haze and become unprintable.

Since LexEdge Clear will often be used in second-surface applications, reverse-print procedures will need to be followed. LexEdge Clear is shipped with the print surface rolled out. When printing on LexEdge Clear, a specific color of foil will often be used as a solid backing color. This color will generally be assigned as an overprint. In order to ensure that this color covers the other printed graphics as completely as possible, it may be necessary to alter its print

settings. (This will be especially needed when the backing foil will be printed on top of more than two other colors.)

The print settings for the backing foil can be changed in the QuickPlot screen. Go into the “Print Order” screen (F11) and select SETTINGS. Click on “DARK” in the overprint side only.

GerberColor Spot (GCS) Series, GerberColor Process (GCP) SUPER CMYK™ Series, and GerberColor Transparent (GCT) Series Foils can be used to print onto LexEdge Clear printing with the Gerber Edge®

LexEdge Clear palettes and print settings are available in GRAPHIX ADVANTAGE® 6.21 Service Pack 1 and higher for the GERBER EDGE. If your GA™ software does not have palettes for LexEdge Clear use 3M Scotchcal 220 dark print settings for the GERBER EDGE. Printing with the Gerber Edge 2

Note: At this point in time, the same settings can be used with the GERBER EDGE® 2 however optimal EDGE 2 print settings will be released in the near future. Until that time, LexEdge Clear will print on the EDGE 2 using GERBER EDGE settings.

CUTTING

LexEdge Clear should be score cut on any 15” GRAPHIX ADVANTAGE® compatible plotter. A 45° SuperSharp blade is recommended. Plotters should be set at 50% speed.

The ideal cut will penetrate halfway through the material. To punch out your finished pieces, find a straight cutline and fold the material backwards. Pinch the cut line with your fingers and the material will break. Slowly remove the finished piece one edge at a time. The user should perform a test cut to determine tool force setting.

If using a plotter with a swivel blade, you will be able to cut simple shapes easily. However, when cutting complex shapes, your ability to maintain an accurate and consistent cut depth may be compromised.

SHELF LIFE AND STORAGE

Store LexEdge Clear in the plastic bag provided in the original shipping box. Printed or unprinted LexEdge Clear should not be stored on a roll that has less than a 3” inside diameter. Use a paper interleaf between printed materials that are rolled or stacked. Do not store printed graphics face to face. LexEdge Clear should be stored in a clean area free from excessive moisture and sunlight. An ambient temperature below 100° F (38°C) is recommended. Unprinted LexEdge Clear can be stored for one year at 70°F (21°C) and 50% relative humidity.

MAINTENANCE

To clean printed graphics, use a mild, non-abrasive soap with a soft cloth or sponge. Avoid using alcohol-based cleansers or soaps containing grit or abrasives.

Physical Properties

Thickness	10 Mil
Film Color	Polished/Polished

CHEMICAL RESISTANCE (UNPRINTED)

Chemical Agent	Result
Mild Acids	No effect
Alcohols	Hazing
Alkalis	No effect at low concentration and below 85° F (29° C). Higher concentrations and temperatures result in physical decomposition.
Aliphatic Hydrocarbons	No effect
Amines	Crystallization
Aromatic Hydrocarbons	Severe Stress cracking
Detergents and sprays	Mild soap solutions have no effect. Strongly alkaline materials should be avoided.
Esters	Crystallization
Fruit juices/soft drinks	End user test recommended
Ketones	Crystallization/stress cracking
Silicone oils/greases	No effect up to 85° F (29° C).

RELATED LITERATURE (PRODUCT BULLETINS)

- ◆ GerberColor Spot (GCS) Series
- ◆ GerberColor Process (GCP) SUPER CMYK Series
- ◆ GerberColor Medal (GCM) Series
- ◆ GerberColor Transparent (GCT)
- ◆ GerberColor Special Effect Series Fluorescent Foils (GCX) Gerber Series

Note: For help with questions concerning Gerber products, please call your distributor or Gerber Customer Service at 1-800-222-7446 or (860) 643-1515.

GRAPHIX ADVANTAGE is a Registered Trademark of Gerber Scientific Products, Inc. LexEdge Clear, GerberColor, and GerberColor SUPER CMYK are Trademarks of Gerber Scientific Products, Inc. Lexan is a registered trademark of the GE Plastics Corporation.

©2009 Gerber Scientific, Inc. All Right Reserved

Category: EDGE READY™ FastFact #:5504 Supplied by: Aftermarkets Last Modified: 4/1/09